HYDAC INTERNATIONAL





LF & LFF Series Service and Parts

up to 174 GPM(660 l/min), up to 1500PSI(100bar)

1. Maintenance

1.1 General

Please follow the maintenance instructions.

1.2 Installation

Before installing the filter into the system, check that the operating pressure of the system does not exceed the permitted operating pressure of the filter.

Refer to the type code label on the filter.

Important

When using filters without bypass valve and at operating pressures above 20 bar (290 psi), filter elements of the type BH/HC must be used for safety reasons.

1.3 Commissioning

Check that the correct filter element is installed. Screw in bowl again fully and then unscrew by one quarter-turn (the sealing effect will not be improved by overtightening).

Switch on the hydraulic system and check filter for leakage.

Vent filter at an appropriate point in the system.

Under extreme conditions (e.g. cold start), bypass valves will allow a partial flow past the element for a short time.

1.4 Maintenance Tools

Size	Wrench for filter bowl	Allen Key for Oil drain plug	Wrench for VD 0 A.1	
30	Hex 24	Hex 6*	Hex 27	
60-140	Hex 27	Hex 10*	Hex 27	
160-280	Hex 32	Hex 10*	Hex 27	
330-4000	Hex 36	Hex 10	Hex 27	

^{*}for SO184

1.5. Torque Values

Туре	Torque in Nm [ft-lb]		
VD – clog ind	33 [24]		
Oil Drain Plug	G1/2 - 52[38] G1/4 - 19[14]		
Bowl/Lid or end cover	Do not torque See 1.3 and 2.2		

2. Element Replacement

2.1 Element Removal

- 1. Switch off hydraulic system and release filter pressure.
- Remove oil drain plug (if present). Drain oil into container.
- Unscrew filter bowl (drain fluid into a suitable container and clean or dispose of it in accordance with environmental regulations).
- Remove filter element from nozzle in filter head (check surface of element for contamination residue and larger particles; these can indicate damage to components).
- Replace or clean filter element (only W/HC (wire screen) and V (metal fiber) elements can be cleaned).
- 6. Clean filter bowl and filter head; particular attention must be given to the threads.
- Examine filter, especially sealing surfaces, for mechanical damage.
- 8. Check O-rings and replace parts if necessary.

2.2 Element Installation

- 1. Lubricate the sealing surfaces and thread on the filter head and bowl, as well as the O-ring, with clean operating fluid.
- When installing a new filter element, check that the designation corresponds to that of the old element.
- 3. Place filter element carefully on to the nozzle.
- 4. Apply silver grade anti-seize (per Mil-PRF-907E) to threads.
- 5. Screw in filter bowl fully (metal to metal contact).
- 6. Screw in oil drain plug (if present).
- 7. Unscrew filter bowl by one quarterturn.
- 8. Switch on hydraulic system and vent filter at a suitable point in the system.
- 9. Check filter for leakage.

NOTE:


Contamination or incomplete pressure release on disassembly can lead to seizing of the bowl thread.

Filter elements which cannot be cleaned must be disposed of in accordance with environmental protection regulations.

FILTER MAINTENANCE

3. Spare Parts

3.1. LF 30 - 660; LFF 60 - 240



Item	Consists	Description	LF 30	LF/LFF 60	LF / LFF 110	LF / LFF 160	LF / LFF 240	LF / LFF 280	LF 330	LF 660	
1.		Filter element	see Point 4. Replacement Elements								
	1.1	Filter element	0030 D	0060 D	0110 D	0160 D	024 D	024 D	0330 D	0660 D	
	1.2	O-ring	12.37 x 2.62*	22 x 3	22 x 3	34 x 3	34 x 3	34 x 3	48 x 3	48 x 3	
2.		Clogging indicator or indicator plug	See Point 5. Replacement Clogging Indicator								
	2.1	Indicator plug VD 0 A.1 VD 0 A.1 /-V	00305932 00305931								
	2.2	Profile seal ring	VM								
	2.3	O-ring	15 x 1.5								
3.		Repair kit LF Repair kit LF /-V	00305791 00305792	01260990 00302094		00305264 00304037			00302270 00302271		
	3.1	O-ring (element)	12.37 x 2.62*	22 x 3 59 x 3 DF60		34 x 3		48 x 3			
	3.2	O-ring (bowl)	46 x 3			80 x 4		117 x 4			
	3.3	Back-up ring (bowl)	DF30			DF160		DF330			
	3.4	Profile seal ring (indicator)	VM	VM	1	VM			VM		
	3.5	O-ring (indicator)	15 x 1.5	15 x 1.5 G 1/2		15 x 1.5		15 x 1.5			
	3.6*	Oil drain plug	G 1/4			G 1/2		G 1/2			
4.		Bowl Assembly Bowl Assembly /-V		302807 1261280	305492 1261281	303039 1261282	304046 1261283	2207296 2207297	303268 1261284	303720 1261285	
	4.1	Bowl	Consult HYDAC	BOWL LF60	BOWL LF110	BOWL LF160	BOWL LF240	BOWL LF280	BOWL LF330	BOWL LF660	
	4.2	O-ring (bowl)	1	59 x 3	59 x 3	80 x 4	80 x 4	80 x 4	117 x 4	117 x 4	
	4.3	Back-up ring (bowl)	1	LF60	LF110	LF160	LF240	LF280	LF330	LF660	


^{*}If present. - O-Ring durometer can range from 70-80Sh. EPR Seal Kits available on request.
- Bowl assembly kits on request – kits include complete bowl with seals and plug(if present).
*(AS568A-112)

4. Replacement Element Model Code

```
0030 D 003 ON / V
Size
  0030, 0060, 0110, 0160,
  0240, 0280, 0330, 0660
Filtration Rating (micron)
  1, 3, 5, 10, 15, 20 = ON
                           3, 5, 10, 20 = BH4HC
  25, 74, 149 = W/HC
                           3, 5, 10, 20 = V
Element Media
  ON, BH4HC, W/HC, V
Seals
  (omit)
           Nitrile rubber (NBR)
           = Fluorocarbon elastomer (FKM)
  EPR
           = Ethylene propylene rubber (EPR)
Supplementary Details -
  SO263 = Modification of elements for Skydrol or HYJET phosphate ester fluids
           = Modification of "V" elements for use with oil water emulsions (HFA) and water polymer solutions (HFC)
```

5. Clogging Indicator Model Code

= Element specially designed to minimize electrostatic charge generation



 $Model\ Codes\ Containing\ RED\ are\ non-stock\ items-Minimum\ quantities\ may\ apply-Contact\ HYDAC\ for\ information\ and\ availability$

FILTER MAINTENANCE

6. Maintenance Instructions

6.1 User Instructions for Filters



- This pressure equipment must only be put into operation in conjunction with a machine or system.
- The pressure equipment must only be used as stipulated in the operating instructions of the machine or system.
- This pressure equipment must only be operated using hydraulic or lubricating fluid.
- It is the responsibility of the operator to comply with the water regulations of the country concerned.



This symbol denotes safety precautions, the non-observance of which can endanger persons and the environment.

CAUTION

- The user must take appropriate action (e.g. venting) to prevent the formation of air pockets.
- Repairs, maintenance work and commissioning must only be carried out by trained personnel.
- Allow the pressure equipment to cool before handling.
- The stipulations of the operating instructions of the machine or the system must be followed.
- Statutory accident prevention regulations, safety regulations and safety data sheets for fluids must be observed.
- · Filter housing must be grounded.
- When working on, or in the vicinity of, hydraulic systems, open flames, sparks and smoking are forbidden.
- Hydraulic oils and water-polluting fluids must not be allowed to
 enter the soil or watercourses or sewer systems. Please ensure safe
 and environmentally friendly disposal of hydraulic oils. The relevant
 regulations in the country concerned with regard to ground water
 pollution, used oil and waste must be complied with.
- Whenever work is carried out on the filter, be prepared for hot oil to escape which can cause injury or scalding as a result of its high pressure or temperature.

DANGER!

- Caution: pressure equipment! Before any work is carried out on the pressure equipment, ensure the pressure chamber concerned (filter housing) is depressurized
- On no account must any modifications (welding, drilling or opening by force, etc.) be carried out on the pressure equipment.
- When using electrical clogging indicators, the electrical power supply to the system must be switched off before removing the clogging indicator connector.

6.2 Maintenance, General

This section describes maintenance work which must be carried out periodically. The operational safety and life expectancy of the filter, and whether it is ready for use, depend to a large extent on regular and careful maintenance.

6.3 Maintenance Measures

- Spare parts must fulfil the technical requirements specified by the manufacturer.
 - This is always ensured when using original HYDAC spare parts.
- Keep tools, working area and equipment clean.
- After disassembling the filter, clean all parts, check for damage or wear and replace parts if necessary.
- When changing a filter element, a high level of cleanliness must be observed.

6.4 Interval Between Element Changes

In principle we recommend that the filter element is changed every 6 months or upon indication, whichever occurs first.

We recommend installing the filter with a clogging indicator (visual and/or electrical or electronic) to monitor the filter element.

If the clogging indicator responds, it is necessary to change or clean the filter element without delay (only W and V elements can be cleaned).

When no clogging indicator has been installed, we recommend changing the elements at specific intervals. (The frequency of changing the filter elements depends on the filter design and the conditions under which the filter is operated). When filter elements are subject to high dynamic loading it may prove necessary to change them more frequently. The same applies when the hydraulic system is commissioned, repaired or when the oil is changed

The standard clogging indicators only respond when fluid is flowing through the filter. With electrical indicators the signal can also be converted into a continuous display on the control panel. In this case the continuous display must be switched off during a cold start or after changing the element.

If the clogging indicator responds during a cold start only, it is possible that the element does not yet need to be changed.

Customer Information in respect of Machinery Directive 2006/42/EC

Hydraulic filters are defined as fluid power parts / components and are therefore excluded from the scope of the Machinery Directive, sections 1.4.1 - 1.4.3. They do not bear the CE mark.

Before using these components, ensure compliance with the specifications provided by HYDAC Technology Corporation. The specifications also contain information on the relevant essential health and safety requirements (based on Machinery Directive 2006/42/EC).

We hereby declare that the filters are intended to be incorporated into machinery within the terms of the Directive 2006/42/EC. It is prohibited to put the filters into service until the machinery as a whole is in conformity with the provisions of the Machinery Directive.

Service address

HYDAC Technology Corporation Filter Division

2260 City Line Road Bethlehem, PA 18017 +1.610.266.0100

NOTE


The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

FILTER MAINTENANCE

Notes



DAC INTERNATIONAL

Global Headquarters HYDAC INTERNATIONAL GMBH

Industriegebiet D - 66280 Sulzbach/Saar Germany

Tel.: +49 6897 509-01

Fax: +49 6897 509-577

Internet: www.hydac.com Email: info@hydac.com

North America Locations

North America Headquarters **HYDAC TECHNOLOGY CORPORATION Filter Division**

2260 City Line Road Bethlehem, PA 18017

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION Filter System Division Process Filter Division

Fuel Filtration Division 580 West Park Road Leetsdale, PA 15056

+1.724.318.1100

HYDAC TECHNOLOGY CORPORATION **Cooling System Division**

1051 Airlie Parkway Denver, NC 28037

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION Sales Office & Operations

510 Stonegate Drive Katy, TX 77494

+1.281.579.8100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **SE Sales Office**

1051 Airlie Parkway Denver, NC 28037

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION **Electronic Division**

Process Filter Division HYDAC CORPORATION **Accumulator Division**

90 Southland Drive Bethlehem, PA 18017

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION Hydraulic Division -Compact Hydraulics

450 / 445 Windy Point Drive Glendale Heights, IL 60139

+1.630.545.0800

www.HYDAC-NA.com

HYDAC TECHNOLOGY CORPORATION Accessory Division

2204 Avenue C Bethlehem, PA 18017 +1.610.266.0100

HYDAC TECHNOLOGY CORPORATION Hydraulic Division - Tech Center

430 Windy Point Drive Glendale Heights, IL 60139

+1.630.545.0800

HYDAC TECHNOLOGY CORPORATION **Mobile Hydraulic Division**

1660 Enterprise Parkway • Suite E Wooster, OH 44691

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **NW Sales Office & Operations**

1201 NE 144th St. Bldg. B • Suite 111 Vancouver, WA 98685

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **NC Sales Office**

9415 West Forest Home Ave. • Suite 200 Hales Corners, WI 53130

+1.610.266.0100

HYDAC CYLINDERS LLC 540 Carson Road North Birmingham, AL 35217

+1.205.520.1220

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **NE Sales Office**

1660 Enterprise Parkway . Suite E Wooster, OH 44691

+1.610.266.0100

Canada

HYDAC CORPORATION

14 Federal Road Welland, Ontario, Canada L3B 3P2

+1.905.714.9322

HYDAC CORPORATION Sales Office

5160 75 Street NW Edmonton, Alberta, Canada T6E 6W2

+1.780.484.4228

www.HYDAC-NA.com

HYDAC CORPORATION Sales Office

Montreal, Québec, Canada J2M 1K9

+1.877.539.3388

Mexico

HYDAC INTERNATIONAL SA de CV

Calle Alfredo A Nobel No 35 Col Puente de Vigas Tlalnepantla, Edo Mexico CP 54090 Mexico

+011.52.55.4777.1262

www.HYDACmex.com