# HYDAC INTERNATIONAL



## **Filters**

# DFN, DFNF, LFN & LFNF Series Service and Parts in accordance with DIN 24550

up to 106 gpm (400 l/min), up to 5800 psi (400 bar)

#### 1. Maintenance

#### 1.1 General

Please follow the maintenance instructions.

#### 1.2 Installation

Before installing the filter into the system, check that the operating pressure of the system does not exceed the permitted operating pressure of the filter.

Refer to the type code label on the filter.

#### Important:

When using filters without bypass valve and at operating pressures above 290 psi (20 bar), high differential pressure-resistant filter elements of the type BH4HC should be used for safety reasons.

#### 1.3 Commissioning

Check that the correct filter element is installed. Screw in bowl again fully and then unscrew by one quarter-turn (the sealing effect will not be improved by overtightening).

Switch on the hydraulic system and check filter for leakage.

Vent filter at an appropriate point in the system.

Under extreme conditions (e.g. cold start), bypass valves will allow a partial flow past the element for a short time.

#### 1.4 Maintenance Tools

Size	Wrench for filter bowl	Allen key for oil drain plug	Wrech for VD 0 A.1	
40-100	Hex 27	Hex 10	Hex 27	
160-400	Hex 36	Hex 10	Hex 27	

#### 1.5 Torque Values

Type LFN/LFNF	Torque Nm [ft-lb]			
VM/VD	33 [24]			
Type DFN/DFNF	Torque Nm [ft-lb]			
VM	33 [24]			
VD	100 [74] standard			
VD	50 [37] (A, LE, LZ)			
Oil Drain Plug	80 [59] – G½ 30 [22] – G¼			
Bowl/ Lid or end cover	Do not Torque (See 1.3 and 2.2)			

#### 2. Element Replacement

#### 2.1 Element Removal

- 1. Switch off hydraulic system and release filter pressure.
- 2. Remove oil drain plug (if present). Drain oil into container.
- 3. Unscrew filter bowl.
- 4. Remove filter element from element nozzle in filter head (check surface of element for contamination residue and larger particles; these can indicate damage to components).
- Replace or clean filter element only W/HC (wire screen) and V (metal fiber) elements can be cleaned.
- Clean filter bowl and filter head; particular attention must be given to the threads.
- Examine filter, especially sealing surfaces, for mechanical damage.
- 8. Check O-rings and replace if necessary

#### 2.2 Element Installation

- Wet the sealing surfaces and thread on the filter head and bowl, as well as the O-ring on the bowl and element, with clean operating fluid.
- 2. When instaling a new filter element, check that the designation corresponds to that of the old element.
- 3. Place filter element carefully on to the element nozzle.
- Apply silver grade anti-seize (per Mil-PRF-907E) to threads. Screw in filter bowl fully (metal to metal contact).
- 5. Screw in oil drain plug (if present).
- 6. Unscrew filter bowl by one quarter-turn.
- 7. Switch on hydraulic system and vent filter at a suitable point in the system.
- 8. Check filter for leakage.

#### NOTE:


Contamination or incomplete pressure release on disassembly can lead to seizing of the bowl thread.

Filter elements which cannot be cleaned must be disposed of in accordance with environmental protection regulations.

## FILTER MAINTENANCE

#### 3. Spare Parts

### 3.1 DFN, DFNF, LFN, LFNF 40 – 100, DFN 160 – 400




Item	Consists	Designation	40	63	100	160	250	400	
1.		Filter element	See Point 4. Replacement elements						
	1.1	Filter element	0040 DN	0063 DN	0100 DN	0160 DN	0250 DN	0400 DN	
	1.2	O-ring	21.82 x 3.53		40.87 x 3.53				
2.		Clogging indicator or indicator plug	See Point 5. Replacement clogging indicator						
	2.1	Indicator plug VD 0 A.1 VD 0 A.1 /-V	00305932 00305931						
	2.2	Profile seal ring	VM/ VD						
	2.3	O-ring	15 x 1.5						
3.		Repair kit LFN(F) Repair kit LFN(F) /-V Repair kit DFN(F) Repair kit DFN(F) /-V	01264344 01279105 012795871.1 012795881.1			- - 01261131 01261132			
	3.1	O-ring (element)	21.82 x 3.53			40.87 x 3.53			
	3.2 O-ring (bowl)		59 x 3 107.54 x 3.53						
	3.3	Back-up ring (bowl)		DF 60			DFN 160		
	3.4	Profile seal ring (indicator)	VM/ VD						
	3.5	O-ring (indicator)	15 x 1.5						
	3.6*	Oil drain plug	G 1/2						
	3.7*	Vent screw	G 1/8						

Other spare parts & spare parts for other versions (e.g. LFN 1.0) on request.

<sup>\*</sup>Only for DFN(F) filters
- O-Ring durometer can range from 70-80Sh. EPR Seal Kits available on request.
- Bowl assembly kits on request – kits include complete bowl with seals, plug, and threaded pin. (if present)


#### 4. Replacement Element Model Code



Modication of "V" elements for use with oil water emulsions (HFA) and water polymer solutions (HFC) usually polyglycol

Element specially designed to minimize electrostatic charge generation

#### Clogging Indicator Model Code



W = "VD..." indicator modified with a brass piston for use with High water based emulsions/solutions (HFA) & (HFC) (For additional details and options, see Section G - Clogging Indicators of the HYDAC Filter catalog.)



## FILTER MAINTENANCE

#### 6. Maintenance Instructions

#### 6.1 User Instructions for Filters



- This pressure equipment must only be put into operation in conjunction with a machine or system.
- The pressure equipment must only be used as stipulated in the operating instructions of the machine or system.
- This pressure equipment must only be operated using hydraulic or lubricating fluid.
- It is the responsibility of the operator to comply with the water regulations of the country concerned.



This symbol denotes safety precautions, the non-observance of which can endanger persons and the environment.

#### CAUTION

- The user must take appropriate action (e.g. venting) to prevent the formation of air pockets.
- Repairs, maintenance work and commissioning must only be carried out by trained personnel.
- Allow the pressure equipment to cool before handling.
- The stipulations of the operating instructions of the machine or the system must be followed.
- Statutory accident prevention regulations, safety regulations and safety data sheets for fluids must be observed.
- · Filter housing must be grounded.
- When working on, or in the vicinity of, hydraulic systems, open flames, sparks and smoking are forbidden.
- Hydraulic oils and water-polluting fluids must not be allowed to
  enter the soil or watercourses or sewer systems. Please ensure safe
  and environmentally friendly disposal of hydraulic oils. The relevant
  regulations in the country concerned with regard to ground water
  pollution, used oil and waste must be complied with.
- Whenever work is carried out on the filter, be prepared for hot oil to escape which can cause injury or scalding as a result of its high pressure or temperature.

#### **DANGER!**

- Comply with all regulations with regard to the disposal of used oil and waste
- Wear proper protective clothing and guards to avoid injury or scalding due to high pressure or high temperature oil.
- Filter housing must be grounded.
- Disconnect all electrical power to the system and other electrical components, prior to working on filter clogging indicators.
- When using electrical clogging indicators, the electrical power supply to the system must be switched off before removing the clogging indicator connector.

#### 6.2 Maintenance, General

This section describes maintenance work which must be carried out periodically. The operational safety and life expectancy of the filter, and whether it is ready for use, depend to a large extent on regular and careful maintenance.

#### 6.3 Maintenance Measures

- Spare parts must fulfil the technical requirements specified by the manufacturer.
  - This is always ensured when using original HYDAC spare parts.
- Keep tools, working area and equipment clean.
- After disassembling the filter, clean all parts, check for damage or wear and replace parts if necessary.
- When changing a filter element, a high level of cleanliness must be observed.

#### 6.4 Interval Between Element Changes

In principle we recommend that the filter element is changed every 6 months or upon indication, whichever occurs first.

We recommend installing the filter with a clogging indicator (visual and/or electrical or electronic) to monitor the filter element.

If the clogging indicator responds, it is necessary to change or clean the filter element without delay (only W and V elements can be cleaned).

When no clogging indicator has been installed, we recommend changing the elements at specific intervals. (The frequency of changing the filter elements depends on the filter design and the conditions under which the filter is operated). When filter elements are subject to high dynamic loading it may prove necessary to change them more frequently. The same applies when the hydraulic system is commissioned, repaired or when the oil is changed

The standard clogging indicators only respond when fluid is flowing through the filter. With electrical indicators the signal can also be converted into a continuous display on the control panel. In this case the continuous display must be switched off during a cold start or after changing the element.

If the clogging indicator responds during a cold start only, it is possible that the element does not yet need to be changed.

#### Customer Information in respect of Machinery Directive 2006/42/EC

Hydraulic filters are defined as fluid power parts / components and are therefore excluded from the scope of the Machinery Directive, sections 1.4.1 - 1.4.3. They do not bear the CE mark.

Before using these components, ensure compliance with the specifications provided by HYDAC Technology Corporation. The specifications also contain information on the relevant essential health and safety requirements (based on Machinery Directive 2006/42/EC).

We hereby declare that the filters are intended to be incorporated into machinery within the terms of the Directive 2006/42/EC. It is prohibited to put the filters into service until the machinery as a whole is in conformity with the provisions of the Machinery Directive.

#### Service address

HYDAC Technology Corporation Filter Division

2260 City Line Road Bethlehem, PA 18017 +1.610.266.0100

#### NOTE


The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

## FILTER MAINTENANCE

#### **Notes**



## DAC INTERNATIONAL

#### **Global Headquarters HYDAC INTERNATIONAL GMBH**

Industriegebiet D - 66280 Sulzbach/Saar Germany

Tel.: +49 6897 509-01

Fax: +49 6897 509-577

Internet: www.hydac.com Email: info@hydac.com

#### **North America Locations**

North America Headquarters **HYDAC TECHNOLOGY CORPORATION Filter Division** 

2260 City Line Road Bethlehem, PA 18017

+1.610.266.0100

**HYDAC TECHNOLOGY CORPORATION Filter System Division** 

**Process Filter Division Fuel Filtration Division** 580 West Park Road

Leetsdale, PA 15056 +1.724.318.1100

HYDAC TECHNOLOGY CORPORATION **Cooling System Division** 

1051 Airlie Parkway Denver, NC 28037

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION Sales Office & Operations

510 Stonegate Drive Katy, TX 77494

+1.281.579.8100

**HYDAC TECHNOLOGY CORPORATION** HYDAC CORPORATION **SE Sales Office** 

1051 Airlie Parkway Denver, NC 28037

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION **Electronic Division** Process Filter Division

HYDAC CORPORATION **Accumulator Division** 

90 Southland Drive Bethlehem, PA 18017

+1.610.266.0100

**HYDAC TECHNOLOGY CORPORATION Hydraulic Division -Compact Hydraulics** 

450 / 445 Windy Point Drive Glendale Heights, IL 60139

+1.630.545.0800

www.HYDAC-NA.com

**HYDAC TECHNOLOGY CORPORATION Accessory Division** 

2204 Avenue C Bethlehem, PA 18017 +1.610.266.0100

**HYDAC TECHNOLOGY CORPORATION** 

430 Windy Point Drive Glendale Heights, IL 60139

HYDAC TECHNOLOGY CORPORATION **Mobile Hydraulic Division** 

1660 Enterprise Parkway • Suite E Wooster, OH 44691

+1.610.266.0100

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **NW Sales Office & Operations** 

1201 NE 144th St. Bldg. B • Suite 111 Vancouver, WA 98685

+1.610.266.0100

**HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION NC Sales Office** 

9415 West Forest Home Ave. • Suite 200 Hales Corners, WI 53130

+1.610.266.0100

**Hydraulic Division - Tech Center** 

+1.630.545.0800

**HYDAC CYLINDERS LLC** 

540 Carson Road North Birmingham, AL 35217

+1.205.520.1220

HYDAC TECHNOLOGY CORPORATION HYDAC CORPORATION **NE Sales Office** 

1660 Enterprise Parkway . Suite E Wooster, OH 44691

+1.610.266.0100

Canada

HYDAC CORPORATION

14 Federal Road Welland, Ontario, Canada L3B 3P2

+1.905.714.9322

HYDAC CORPORATION Sales Office

5160 75 Street NW Edmonton, Alberta, Canada T6E 6W2

+1.780.484.4228

www.HYDAC-NA.com

HYDAC CORPORATION Sales Office

Montreal, Québec, Canada J2M 1K9

+1.877.539.3388

Mexico

**HYDAC INTERNATIONAL SA de CV** 

Calle Alfredo A Nobel No 35 Col Puente de Vigas Tlalnepantla, Edo Mexico CP 54090 Mexico

+011.52.55.4777.1262

www.HYDACmex.com